

TECHNICAL DATA

Model Number: MD150D050U/D+**Type** Multi--Voltage AC/DC Adaptor**Electrical Data**

Input	Input Voltage/Frequency	230V/50Hz
	Input Power	16W
Output	Rated Output Voltage	15V
	Rated Output Load Current	500mA
	Rated Output Power	7.5 VA
Resistance	Insulation Resistance	100MΩ(measured with 500V DC voltage)
Protection	Thermal Protection	Thermal fuse:125□/2A
	Withstand Voltage (Hi-Pot)	AC 3750V 50Hz for 1minute or AC4000V 2seconds

Mechanical Data

Supply Connection Type	SCHUKO type DIN49 MWST-1 464/F
Primary Turns & Wire Gauge	1550T/0.13mm
Secondary Turns & Wire Gauge	100T/0.55mm
Core Size	48mm×26mm
Output Plug Dimensions	5.0×2.1 ×12mm
Polarity	CENTER POSITIVE
Unit Weight	450g
Dimensions	75(L)×58(W)×87(H)