

## Facom K.33B 3/4" Drive 12 Point Socket 33mm



### Description

**Higher torque without damage to fasteners !**

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

**More powerful tightening:** Larger contact area between socket and fastener minimizes stress.

**Less wear:** Torque is transmitted through the fastener flats instead of the corners.

**Increased durability:** Stress concentration in the corners is eliminated.

### Technical specification:

- 33mm AF 12 point socket with 3/4" drive
- Secure attachment of plunger lock accessories
- Quick release button
- Chrome finish
- Performance : to ISO 2725-1, DIN 3124, NF ISO 2725-5
- Length 59mm
- Weight 0.330kg