

Facom K.38B 3/4" Drive 12 Point Socket 38mm



Description

Higher torque without damage to fasteners !

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

More powerful tightening: Larger contact area between socket and fastener minimizes stress.

Less wear: Torque is transmitted through the fastener flats instead of the corners.

Increased durability: Stress concentration in the corners is eliminated.

Technical specification:

- 38mm AF 12 point socket with 3/4" drive
- Secure attachment of plunger lock accessories
- Quick release button
- Chrome finish
- Performance : to ISO 2725-1, DIN 3124, NF ISO 2725-5
- Length 66.9mm
- Weight 0.478kg