



## **SLW2400** 2400W PIR Light Controller - White

- 12m detection range with 180 area of detection.
- Adjustable light level control.
- IP55 weatherproof rating.
- Adjustable light ON time 5 secs - 12 mins.
- Manual ON/OFF override.
- Hinged back box for ease of wiring.
- Total PIR switching - 2400W incandescent or halogen, 500W fluorescent, 22W low energy.

### Specifications

<b>Operating Voltage</b>	230V AC
<b>Maximum Light Load (W) Tungsten/Halogen External</b>	2400
<b>Maximum Fusing</b>	10A
<b>Weatherproof Rating</b>	IP55
<b>Detection Range (Max) Metres</b>	12
<b>Angle of Detection</b>	180
<b>Light On Time After Last Detection (Adjustable)</b>	5 Seconds (Min) 12 Minutes (Max)
<b>Permanent ON Facility (Electronic)</b>	Electronic
<b>Adjustable Light Level Control</b>	Yes
<b>Conforms to Directives</b>	73/23/EEC, 89/336/EEC
<b>Overall Dimensions (mm)</b>	Width 87, Height 73, Depth 121

Note: SLV101E, SLW2400, SLOD2000 can be wired in parallel to enable any detector to turn ON all of the lights connected to it (the total wattage capability of the unit must not be exceeded). SLV360E's must not be wired in parallel. SLV360E cannot switch relays or contactors.

---

Sales Office Direct Line: 020 8452 1112 Fax: 020 8450 0635 Email:  
[csc@timeguard.com](mailto:csc@timeguard.com)