



Specifications

- | | | |
|----------------------------|-------------|-------------------|
| • Voltage | 7,2 V | • Staple storage |
| • Battery capacity | 1,2 Ah | • Impact control |
| • Number of impacts | 30 per min. | • Safety lock-off |
| • Staple length | 6 - 14 mm | |
| • Staple width | 11,4 mm | |
| • Nails Length | 14 mm | |
| • Loading capacity staples | 70 | |
| • Loading capacity nails | 70 | |
| • Capacity staple storage | 70 | |
| • Charging time | 3 - 5 hrs | |
| • Weight | 1,9 kg | |

Standard equipment

- 7,2 V (1,2 Ah NiCad) integrated battery (Sweden 1,2 Ah NiMH)
- 3 - 5 hour charger
- 1000 staples (11,4 x 8 mm)
- Plastic carrying case

Packaging info

	OEC	UK
Dimensions (WxHxD)	365x321x98	365x321x98
Packed Per	4	4
Per europallet (1,20x0,8m)	72	48

Availability

Products

See Quick Reference Guide

Logistics

	Ordering code	EAN code	EZUG Nr.
Switzerland	F015 2100 AA	8710364034963	056
United Kingdom/Ireland	F015 2100 AB	8710364034970	
Sweden	F015 2100 AC	8710364034987	
Other European Countries	F015 2100 AA	8710364034963	



August 2006