

INTERNAL



IMPACT

full featured internal SAB sounder & strobe unit

The Impact has a translucent 3mm Polycarbonate housing making a low-profile and high security internal sounder and strobe. With a wide variety of options the Impact will have a model to suit any installation.

Sounder	Single Piezo 114 dB @ 1M. Twin Piezo 117dB @ 1M.
Strobe	2 Watt strobe tube.
Tamper	Front and back.
Status LED	Yellow.
Timer	20 minutes and 5 seconds engineer test.
Battery	6 volt.
Speaker	50 Ohm dynamic, 50mm.

TELEPHONE

ultra low profile domestic extension speaker

Fitted with a 50 Ohm dynamic speaker, the Telephone produces just the right amount of sound. Compatible with 8 or 16 Ohm control panel outputs.

SAPPHIRE

modern low profile extension speaker

High impact ABS housing.
8 or 16 Ohm dynamic speaker.
High and low volume piezo sounder model 114dB @ 1M.
Optional front tamper.

SAPPHIRE MKII

commercial extension speaker & sounder

8 or 16 Ohm dynamic speaker.
Sounder Model 108dB @ 1M.
Optional front / back tamper.
Cover screw.

