


**DP SWITCHES
20 AMP**


FLUSH



5403 WHI



5423 WHI




5423 WH WHI



5444 WHI



5445 WHI



5105 WHI



5205 WHI



5215 WHI



5230 WHI

**DP SWITCH
45 AMP
METAL**

SURFACE

- 5403 WHI** 10
DP Switch
- 5423 WHI** 10
With pilot lamp
- 5423 WH WHI** 10
With pilot lamp and
marked "water heater".

- 5444 WHI** 10
With flex outlet
- 5445 WHI** 10
With flex outlet and
pilot lamp

- 5105 WHI** 5
With pilot lamp

- 5205 WHI** 1
- 5215 WHI** 1
With pilot lamp

- 5230 WHI** 1
With pilot lamp

MOUNTING BOXES

Flush: **866 ZIC**
Surface: **2140 WHI**
2031 WHI (for extra
wiring space)

All switches are complete with
earth terminals.

Dimensions:
86 x 86mm

Fixing Centres:
60.3mm

BS.3676 Pt.1: 1989

Accepted by the Design Council
for inclusion in the Design Index

MOUNTING BOXES

Flush: **866 ZIC**
Surface: **2140 WHI**
2031 WHI (for extra
wiring space)

All switches are complete with
earth terminals.

Dimensions:
86 x 86mm

Fixing Centres:
60.3mm

BS.3676 Pt.1: 1989

Accepted by the Design Council
for inclusion in the Design Index

MOUNTING BOXES

Flush:
866 ZIC (6mm² conductors)
877 ZIC (10mm² conductors)

Surface: **2140 WHI** (6mm²
conductors)
2031 WHI (10mm²
conductors)

Supplied with 6 self-adhesive
plastic identification labels
marked hob, oven, water heater,
shower, air conditioner and
cooker.

Dimensions:
86 x 86mm

Fixing Centres:
60.3mm

BS.3676 Pt.1: 1989

MOUNTING BOXES

Flush: **878 ZIC**
Surface: **2172 WHI**

Supplied with 6 self-adhesive
plastic identification labels
marked hob, oven, water heater,
shower, air conditioner and
cooker.

Dimensions:
146 x 86mm

Fixing Centres:
120.6mm

Terminal Capacity:
16mm² conductors

BS.3676 Pt. 1: 1989

Accepted by the Design Council
for inclusion in the Design Index

Earth terminal:
Fitted on base of box.

Also available in Metalclad
version (page 54).

Dimensions:
150 x 89 x 50mm

Knockouts:
8 x 20mm

Terminal Capacity:
16mm² conductors

BS.3676:Pt.1: 1989

Accepted by the Design Council
for inclusion in the Design Index