



datasheet for MLS GG 200/2,5  
 article number: 934077100



<b>product description:</b>	order number: 934 077-100
<b>description:</b>	Safety measuring lead, at either end 4 mm diameter safety connector with straight outlet. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Color indicator for the recognition of damage to the insulation. In accordance DIN EN 61010-031 standard.
<b>typ:</b>	MLS GG 200/2,5 schwarz/black
<b>system:</b>	4 mm safety system
<b>order number:</b>	934 077-100
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category</b>	CAT III
<b>norm</b>	DIN EN 61010-031
<b>pin dimensions</b>	4 mm
<b>type of contact:</b>	spring mounted pin
<b>type of termination:</b>	4 mm diameter pin
<b>cable type:</b>	LEH-XY
<b>cable specification:</b>	high flexible lead
<b>wire stranding:</b>	320 x 0.10
<b>rated voltage:</b>	AC/DC 1000 V
<b>rated current:</b>	32 A
<b>contact resistance:</b>	20 mOhm
<b>cable length:</b>	200 cm
<b>conductor size:</b>	2,5 mm <sup>2</sup>
<b>cable material:</b>	PVC
<b>cable color:</b>	black
<b>material</b>	
<b>contact material:</b>	copper beryllium
<b>contact surface material:</b>	nickel
<b>housing material:</b>	PA
<b>environmental conditions:</b>	
<b>temperature range:</b>	-15 °C to +70 °C

<b>inflammable class:</b>	
<b>housing:</b>	94 V-2
<b>drawing</b>	
	