

tesa® 4574

Monofilament tape

PRODUCT INFORMATION

Product Description

tesa® 4574 is a monofilament tape based on a polypropylene film laminated to glass filaments. tesa® 4574 has a good longitudinal tensile strength.

Main Application

Applications include bundling and strapping heavy goods, securing pallets and closing and reinforcing of shipping cartons.

Technical Data

■ Backing material	glassfibre / BOPP	■ Adhesion to steel	8 N/cm
■ Type of adhesive	synthetic rubber	■ Elongation at break	8 %
■ Total thickness	125 µm	■ Tensile strength	230 N/cm

tesa UK Ltd.

Yeomans Drive, Blakelands
Milton Keynes, Bucks MK 14 5LS
Phone: +44 (1) 908 211 333
Fax: +44 (1) 908 211 555
ukenquiry@tesa.com

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.