

tesa® 51408

Flame retardant Kapton® high grade Masking Tape

PRODUCT INFORMATION

Product Description

tesa® 51408 (Kapton® backing with silicone adhesive) is a highly temperature-resistant and high grade adhesive tape

Main Application

tesa® 51408 can withstand high temperatures for limited periods of time (250°C/ 482 F = 1.000 hours, 350°C/ 662 F = 10 hours).

Technical Data

■ Backing material	Kapton®	■ Elongation at break	60 %
■ Type of adhesive	silicone	■ Temperature resistance	180 °C
■ Total thickness	65 µm	■ Dielectric breakdown voltage	7500 volt
■ Adhesion to steel	2.2 N/cm	■ Volume resistivity	10.14 10 ¹⁴ Ωm

Properties

■ Insulation class	H
--------------------	---

tesa UK Ltd.

Yeomans Drive, Blakelands
Milton Keynes, Bucks MK 14 5LS
Phone: +44 (1) 908 211 333
Fax: +44 (1) 908 211 555
ukenquiry@tesa.com

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.