

tesa® 4662

Strong duct tape

PRODUCT INFORMATION

Product Description

tesa® 4662 is a strong duct tape. It consists of a 27 mesh woven PET/cotton fabric backing coated with a natural rubber adhesive. tesa® duct 4662 is a self adhesive tape with typical duct features for a wide range of applications.

Features:

- excellent adhesion even on rough and dusty surfaces (e.g. brickwork, timber)
- water repellent
- conformable
- available in 3 colours: black, white, silver

Main Application

- Sealing of pipes and ducts
- Bonding of construction and protection films
- Closing of covering foils
- Application on brickwork and timber
- Fixing, closing, packaging and a lot more!

Technical Data

■ Backing material	PE laminated cloth	■ Elongation at break	15 %
■ Type of adhesive	natural rubber	■ Tensile strength	34 N/cm
■ Total thickness	230 µm	■ Mesh	27 count per square inch
■ Adhesion to steel	4.5 N/cm	■ Temperature resistance (30 min)	95 °C

Properties

■ Water resistance	o	■ Hand tearability	+
■ Abrasion resistance	o	■ Straight tear edges	+

Evaluation across relevant tesa® assortment: ++ very good, + good, o medium, - low

tesa UK Ltd.

Yeomans Drive, Blakelands
Milton Keynes, Bucks MK 14 5LS
Phone: +44 (1) 908 211 333
Fax: +44 (1) 908 211 555
ukenquiry@tesa.com