## Product Family Documents

Family Color Selection Guide ctcolor-materials.pdf

- HLS Strip Ties have hooks on one side and loops on the other so it adheres to itself.
- Releasable and reusable hundreds of times.
- No installation tool required.
- No risk of over tensioning and damaging high performance cabling.
- HLSP Series (Black and Maroon) are unique Hook and Loop style ties that are UL Listed (File #E56854) for use in air handling spaces per NEC Section 300-22(c) and (d) and are UL94V-2 flame rated.
- No waste since excess can be wrapped around bundle.
- HLM Series can be used with ABMT, ABM3H, ABM4H and TMEH mounts.
- Operating temperature range: 0 to 220°F

## Note:

 Minimum 2" overlap required to achieve loop tensile rating (HLT, HLS, HLM Series) and UL Listed Rated Load (HLSP Series).HLS, HLSP & HLM SeriesHLM, HLS and HLSP Strips and Rolls

HLS-15R0	
Part Description	Tak-Ty® Hook & Loop Cable Tie, 15' roll, .75" width, Standard, Black Can be cut to desired length, eliminating waste.
Material	Hook & Loop
Color	Black
Length (in)	180.0
Width (in)	.750
Max. Bundle Dia. (in)	Various
Min. Loop Tensile Str. (lbs)	50
UOM	RL
Std. Pkg. Qty.	1
Min. Order Qty	1































Click on image to enlarge...