PV - 90° Resistance Thermometer

90° Resistance Thermometer - For measurement of temperatures in machinery, bearings or general purpose applications. Also where the cable needs to be exiting the sheath at a 90° right angle where room to mount the sensor is restricted

- Resistance type PT100, Class B, 4 wire
- Sheath dimensions are 6mm dia stainless steel × 100mm in length
- Supplied with 2000mm Silicon 4 core cable
- > Temp Range: -50°C to +180°C

Global Part No.

91-9420-03

Description

PRT 90° 6mm x 100mm





