

Language: [HOME](#) [PRODUCTS](#) [SERVICE](#) [CORPORATE](#) [PRESS](#)SEARCH 

Technical specifications



600VA UPS PW-4060T

Technical Specifications

- UPS 600 VA rated power capacity
- Up to 45 minutes back-up time (depending on load)
- 2 secure outputs with surge protection
- 1 surge only output for connecting to conductive load
- Filter to protect telephone, fax or modem with RJ-11 connector
- AVR function to compensate fluctuations in mains voltage
- Line-interactive design, processor actuated
- Normal operating voltage 170 - 280 volts, lower will activate the battery powered mode
- 150 Joule Spike protection
- Clear optical and acoustic indicators for power source and low battery
- Fast back up response time: less than 6 msec
- EMI / RFI noise filtering
- Product size (H x W x D in mm): 147 x 105 x 338
- Connected equipment warranty conditions available in package and on www.trust.com

Package contents

- UPS unit
- 2x loop through power cables
- Multi language user's manual
- Warranty conditions for connected equipment

Minimum System Requirements

- Computer or other electronic device
- 230 VAC power input

More Information

- ▶ [CE declaration of conformity](#)
- ▶ [Warranty](#)

Trust is a registered trademark of Trust Holding N.V.

[Service & Register](#)[Where to buy](#)[Download leaflet](#)[Subscribe to newsletter](#)

More Information

- ▶ [Product overview](#)
- ▶ [More pictures](#)
- ▶ [Download drivers](#)
- ▶ [Download manuals](#)
- ▶ [Power/Energy Protector Warranty](#)
- ▶ [Trust Power Protection](#)
- ▶ [Print](#)

[TERMS OF USE](#) [PRIVACY](#)

Copyright ©1995-2005 by Trust