



TAPE MTG DETAIL  
SCALE 2:1

1. 0.76µm [0.000030] MIN GOLD OVER 1.27µm [0.000050] MIN NICKEL.
  2. PLATING THICKNESS TO BE MEASURED ON SURFACES ACCESSIBLE WITH 0.64 [0.025] DIA SPHERE.
- WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
    - A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
    - B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
  2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
    - A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
    - B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL

DO NOT SCALE PRINT. UNLESS SPECIFIED IN DIMENSIONS IN MILLIMETERS (INCHES) TOLERANCES ON: 1. DIMENSIONS IN MILLIMETERS 2. PLG DEC ± .005 3. PLG DEC ± .005 ANGLES ± .5°	DR 04/07/93 D. SELTZ CHK 4-26-93 R. STONE APPD 4-29-93 R. S. KLINE	NAME <b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608
PIN BODY: COPPER ALLOY SPRING: STAINLESS STEEL	APPLICATION SPEC	CONTACT ASSEMBLY, PIN, #16, 16-18 AWG, TYPE 11
FINISH PIN BODY: $\Delta$	SCALE 10:1	DRAWING NO C-202507
SMALL PACK TAPE MTG (SEE DETAIL) $\Delta$	202507-3	
STANDARD	202507-2	
PACKAGING TYPE	202507-1	
	PART NO	

CUSTOMER DRAWING

202507