

### Side Cutters



Model/Order No.	Description
<b>EROP355</b>	Side cutter, semi flush cut, burnished, ESD safe, max. Cu 1,0 mm, 110 mm, 61 g



<b>EROP155</b>	Side cutter, semi flush cut, burnished, ESD safe, max. Cu 1,0 mm, 110 mm, 72 g
----------------	--



<b>EROP419</b>	Side cutter, semi flush cut, burnished, ESD safe, max. Cu 2,0 mm, 130 mm, 110 g
----------------	---



<b>EROP357</b>	Side cutter, semi flush cut, burnished, ESD safe, max. Cu 0,6 mm, 110 mm, 61 g
----------------	--

### Tip Cutters



Model/Order No.	Description
<b>EROP331</b>	Tip cutter, flush cut, burnished, ESD safe, max. Cu 1,5 mm, 120 mm, 81 g



<b>EROP330</b>	Tip cutter, flush cut, burnished, ESD safe, max. Cu 1,0 mm, 130 mm, 84 g
----------------	--

## EROP

## Cutters and Pliers

## Pliers



Model/Order No.	Description
<b>EROP172</b>	Round nose plier, burnished, ESD safe, 125 mm, 63 g



<b>EROP174</b>	Needle nose plier, burnished, ESD safe, 120 mm, 66 g
----------------	---



<b>EROP277</b>	Needle nose plier, burnished, ESD safe, 140 mm, 90 g
----------------	---



<b>EROP280</b>	Needle nose plier, burnished, ESD safe, 170 mm, 113 g
----------------	--



<b>EROP170</b>	Flat nose plier, burnished, ESD safe, 120 mm, 63 g
----------------	---



<b>EROP171</b>	Flat nose plier, burnished, ESD safe, 120 mm, 67 g
----------------	---