

RPD58 BENCH DRILL

RPD58		
Drill Capacity	16mm (5/8")	16mm (5/8")
Speeds	450, 700, 1080 1680, 2600	550, 850, 1310 2035, 3145
Motor 1PH	3/4 HP (INT)	3/4 HP (INT)
Distance - Spindle to Base	660mm (26")	660mm (26")
Distance - Spindle to Column	178mm (7")	178mm (7")
Max Distance - Spindle to Table	490mm (19 1/4")	490mm (19 1/4")
Spindle Stroke / Depth of Cut	78mm (3 1/16")	78mm (3 1/16")
Column Diameter	70mm (2 3/4")	70mm (2 3/4")
Table Tilt	0 - 90°	0 - 90°
Spindle Type	No. 2 MT	No. 2 MT
Table Size	Hex Width (A/C) 320mm (12 9/16") Front to Back (A/F) 280mm (11")	Hex Width (A/C) 320mm (12 9/16") Front to Back (A/F) 280mm (11")
Base Size	Hex Width (A/C) 330mm (13") Front to Back (A/F) 290mm (11 7/16")	Hex Width (A/C) 330mm (13") Front to Back (A/F) 290mm (11 7/16")
Overall Dimension		
Height	1060mm (41 3/4")	1060mm (41 3/4")
Width	350mm (13 3/4")	350mm (13 3/4")
Front to Back	657mm (25 7/8")	657mm (25 7/8")
Weight	77kg (169lb)	77kg (169lb)

7141233

RPD58P PEDESTAL DRILL

RPD58P		
Drill Capacity	16mm (5/8")	16mm (5/8")

