

Selection of 12 drain-plug bits

D.108J12

- Supplied on a rack.
 - Comprising :
 - 4 male bits \square 8-10-10.5 and 13.1 mm.
 - 1 female bit \triangleright 10 mm.
 - 1 female bit \square 10 mm.
 - 6 hexagon male bits 8-10-12-13-14 and 17 mm.
- $\Delta\Delta$: 550 g.



3/8" drain plug bit with 10 mm female square

D.106-10

- Drive \square 3/8" (Junior).
 - \square 10 mm.
- $\Delta\Delta$: 40 g.



3/8" drain plug bit with male triangle

D.109-10

- Drive \square 3/8" (Junior).
 - \triangleright 10 mm.
- $\Delta\Delta$: 40 g.



► Oil-filter wrenches

Fast oil-filter wrench

U.46ACL


- High-strength smooth stainless steel band wrench.
 - Sprung hinged jaw grips filter and provides ratchet effect.
 - Resilient glass fibre reinforced composite handle (resistant to hydrocarbons, impact, etc.).
 - Multi-thread adjustment screw for fast pre-tightening.
 - Dimensions : 290 x 45 x 45 mm.
 - Ratchet effect and 5° increments.
 - Handle length : 175 mm.
- \varnothing 66 to 106 mm filters.
 $\Delta\Delta$: 345 g.



	Description
U.46CLO6	Stainless steel strap

D.105 3/8" drain plug bits with male square

- Square drive : \square 3/8" (Junior).


	\square mm	$\Delta\Delta$ g
D.105-8	8	30
D.105-10	10	35
D.105-10,5	10,5	35
D.105-13,1	13,1	60



D.107 3/8" drain plug bits with 10 mm male hexagon.

- Square drive : \square 3/8" (Junior).



	\varnothing mm	$\Delta\Delta$ g
D.107-8	8	30
D.107-10	10	35
D.107-12	12	35
D.107-13	13	40
D.107-14	14	40
D.107-17	17	50

Drain plug bit

D.120-16

- XZN pattern \varnothing 16 mm.
 - Drive \square 3/8" (Junior).
- >> V.A.G. gearbox.
 $\Delta\Delta$: 40 g.



Oil change and filter module

MOD.U46CLPB

- 13 drain plug bits \square 3/8" :
 - D.105-8-10-10.5-13.1.
 - D.106-10.
 - D.107-8-10-12-13-14-17.
 - D.109-10.
 - D.120-16.
 - Fast oil-filter wrench U.46ACL
 - Coupler S.230 \square 1/2" \square 3/8".
- $\Delta\Delta$ 1.1 kg.

