

Product Datasheet Mini 3U Energy Saving Lamps



MINI 3U 5W E14	Mini Energy Saving Lamp 5W (25W) E14
MINI 3U 8W E27	Mini Energy Saving Lamp 8W (40W) E27
MINI 3U 11W E27	Mini Energy Saving Lamp 11W (60W) E27
MINI 3U 14W E27	Mini Energy Saving Lamp 14W (75W) E27
MINI 3U 8W B22	Mini Energy Saving Lamp 8W (40W) B22
MINI 3U 11W B22	Mini Energy Saving Lamp 11W (60W) B22
MINI 3U 14W B22	Mini Energy Saving Lamp 14W (75W) B22

Available as:

- Type: Warm light or Daylight
- Wattage: 9W, 11W, 15W and 18W
- Fitting: BC (B22) SES (E14) and ES (E27)

Features

- Energy Rating 'A'. Up to 80% energy saving compared to traditional bulbs by using less electricity to reach the equivalent brightness:
 - 9 WATTS = 40 WATTS for a conventional bulb
 - 11 WATTS = 60 WATTS for a conventional bulb
 - 15 WATTS = 75 WATTS for a conventional bulb
 - 18 WATTS = 100 WATTS for a conventional bulb
- Lamp life up to 8000 hours (8 times longer than conventional GLS lamps)
- Not suitable for dimming, electronic switches, photocells, timing devices, dusk to dawn sensors.
- Instant start up
- No flicker and no filament to burn out!
- Switching does not reduce lamp life
- Excellent colour render
- RoHS Compliant