

# LEAD SPECIFICATION SHEET



**Computer Cables and  
Networking Systems**

Description: SCSI Cable

Part No.: 1530-2

Reference: Farnell Part No. 129768

Length: 2 Mtr

Packaging Instructions  
Individually Bag

Colour: Beige

Box Qty.: 20

Labelling Instructions  
Label With Farnell Part No. **129768** on each bag

Box Type: D

Connector A	Connector B
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
25	25
26	26
27	27
28	28
29	29
30	30
31	31
32	32
33	33
34	34
35	35
36	36
37	37
38	38
39	39
40	40
41	41
42	42
43	43
44	44
45	45
46	46
47	47
48	48
49	49
50	50
Shell	Shell

Connector A  
50 Way Solder type Micro D Plug

Connector B  
50 Way Solder type Micro D Plug

Hood A  
Fully moulded with Clip Fittings

Hood B  
Fully moulded with Clip Fittings

Cable Type  
UL Style 2919 25 Twisted Pair  
(Foil & Braid Screen)

Origination Date - 02/06/97  
Last Modified - 02/06/97  
Country Of Origin - China  
  
©Videk Ltd. London NW9 8RW.  
Tel 0181 200 1122 Fax 0181 200 6494  
Email sales@videk.co.uk