

CAT5e Snagless UTP Networking Cable



- Snagless moulded connector to protect RJ45 tab from damage
- Tested to provide a direct connection to a 10/100Base-T Ethernet network
- Data transmission of up to 100Mbps
- Performance tested to 100MHz frequency

Length	Grey	Blue	Red	Yellow	
0.5m	A3L791b50CM-S	A3L791b50CM-BLS	A3L791b50CM-RDS	A3L791b50CM-YLS	
1m	A3L791b01M-S	A3L791b01M-BLUS	A3L791b01M-REDS	A3L791b01M-YLWS	
2m	A3L791b02M-S	A3L791b02M-BLUS	A3L791b02M-REDS	A3L791b02M-YLWS	
3m	A3L791b03M-S	A3L791b03M-BLUS	A3L791b03M-REDS	A3L791b03M-YLWS	
5m	A3L791b05M-S	A3L791b05M-BLUS	A3L791b05M-REDS	A3L791b05M-YLWS	
10m	A3L791b10M-S	A3L791b10M-BLUS	A3L791b10M-REDS	A3L791b10M-YLWS	
15m	A3L791b15M-S	A3L791b15M-BLUS	A3L791b15M-REDS	A3L791b15M-YLWS	
30m	A3L791b30M-S	A3L791b30M-BLUS	A3L791b30M-REDS	A3L791b30M-YLWS	
Length	Green	Black	White	Orange	Pink
0.5m	A3L791b50CM-GRS	A3L791b50CM-BKS	A3L791b50CM-WHS	A3L791b50CM-ORS	A3L791b50CM-PKS
1m	A3L791b01M-GRNS	A3L791b01M-BLKS	A3L791b01M-WHTS	A3L791b01M-ORGS	A3L791b01M-PNKS
2m	A3L791b02M-GRNS	A3L791b02M-BLKS	A3L791b02M-WHTS	A3L791b02M-ORGS	A3L791b02M-PNKS
3m	A3L791b03M-GRNS	A3L791b03M-BLKS	A3L791b03M-WHTS	A3L791b03M-ORGS	A3L791b03M-PNKS
5m	A3L791b05M-GRNS	A3L791b05M-BLKS	A3L791b05M-WHTS	A3L791b05M-ORGS	A3L791b05M-PNKS
10m	A3L791b10M-GRNS	A3L791b10M-BLKS	A3L791b10M-WHTS	A3L791b10M-ORGS	A3L791b10M-PNKS
15m	A3L791b15M-GRNS	A3L791b15M-BLKS	A3L791b15M-WHTS	A3L791b15M-ORGS	A3L791b15M-PNKS
30m	A3L791b30M-GRNS	A3L791b30M-BLKS	A3L791b30M-WHTS	A3L791b30M-ORGS	A3L791b30M-PNKS

CAT5e Booted UTP Networking Cable



- Booted connector mould to protect RJ45 tab from damage
- Tested to provide a direct connection to a 10/100Base-T Ethernet network
- Data transmission of up to 100Mbps
- Performance tested to 100MHz frequency

Length	Grey	Blue	Red	Yellow	Green	Black
0.5m	A3L791b50CM-B	A3L791b50CM-BLB	A3L791b50CM-RDB	A3L791b50CM-YLB	A3L791b50CM-GNB	A3L791b50CM-BKB
1m	A3L791b01M-B	A3L791b01M-BLUB	A3L791b01M-REDB	A3L791b01M-YLWB	A3L791b01M-GRNB	A3L791b01M-BLKB
1.5m	A3L791b1.5M-B	A3L791b1.5M-BLB	A3L791b1.5M-RDB	A3L791b1.5M-YLB	A3L791b1.5M-GRB-	-
2m	A3L791b02M-B	A3L791b02M-BLUB	A3L791b02M-REDB	A3L791b02M-YLWB	A3L791b02M-GRNB	A3L791b02M-BLKB
3m	A3L791b03M-B	A3L791b03M-BLUB	A3L791b03M-REDB	A3L791b03M-YLWB	A3L791b03M-GRNB	A3L791b03M-BLKB
5m	A3L791b05M-B	A3L791b05M-BLUB	A3L791b05M-REDB	A3L791b05M-YLWB	A3L791b05M-GRNB	A3L791b05M-BLKB
7.5m	A3L791b7.5M-B	A3L791b7.5M-BLB	A3L791b7.5M-RDB	A3L791b7.5M-YLB	A3L791b7.5M-GRB	-
10m	A3L791b10M-B	A3L791b10M-BLUB	A3L791b10M-REDB	A3L791b10M-YLWB	A3L791b10M-GRNB	A3L791b10M-BLKB
15m	A3L791b15M-B	-	A3L791b15M-REDB	A3L791b15M-YLWB	A3L791b15M-GRNB	A3L791b15M-BLKB
25m	A3L791b25M-B	-	-	-	-	A3L791b25M-BLKB
30m	A3L791b30M-B	-	-	-	-	-

CAT5e Assembled UTP Networking Cable



- Assembled plug connection type
- Tested to provide a direct connection to a 10/100Base-T Ethernet network
- Data transmission of up to 100Mbps
- Performance tested to 100MHz frequency

Length	Grey	Blue	Red	Yellow	Green	Black
0.5m	A3L791b50CM-GRY	A3L791b50CM-BLU	A3L791b50CM-RED	A3L791b50CM-YLW	A3L791b50CM-GRN	A3L791b50CM-BLK
1m	A3L791b01M-GRY	A3L791b01M-BLU	A3L791b01M-RED	A3L791b01M-YLW	A3L791b01M-GRN	A3L791b01M-BLK
2m	A3L791b02M-GRY	A3L791b02M-BLU	A3L791b02M-RED	A3L791b02M-YLW	A3L791b02M-GRN	A3L791b02M-BLK

3m A3L791b03M-GRY A3L791b03M-BLU A3L791b03M-RED A3L791b03M-YLW A3L791b03M-GRN A3L791b03M-BLK
5m A3L791b05M-GRY A3L791b05M-BLU A3L791b05M-RED A3L791b05M-YLW A3L791b05M-GRN A3L791b05M-BLK
10m A3L791b10M-GRY A3L791b10M-BLU A3L791b10M-RED A3L791b10M-YLW A3L791b10M-GRN A3L791b10M-BLK
15m A3L791b15M-GRY A3L791b15M-BLU A3L791b15M-RED A3L791b15M-YLW A3L791b15M-GRN A3L791b15M-BLK

CAT5e Booted Networking Cable - multi-packs



- Belkin CAT5e Booted UTP networking cables in packs of 25, 30 and 50

Length	Grey	Blue	Green	1 Pack Contains
0.5m	A3L791b.5MB-50	-	-	50 pcs
1m	A3L791b1M-B-50	-	-	50 pcs
2m	A3L791b02MB-30	A3L791b02MBB-30	A3L791b02MBG-30	30 pcs
3m	A3L791b03MB-30	A3L791b03MBB-30	A3L791b03MBG-30	30 pcs
5m	A3L791b05MB-25	A3L791b05MBB-25	-	25 pcs
10m	A3L791b10MB-25	A3L791b10MBB-25	-	25 pcs