HP Photosmart 335 Compact Photo Printer





Take it to a party and print photos for your friends!

Take this portable photo printer with you wherever you go. Print fun photos directly from your memory card¹, PictBridge-enabled camera or Bluetooth® camera phone². Select photos via built-in 3.8 cm colour LCD.

The HP Photosmart 335 Compact Photo Printer is designed for young people who enjoy socialising and want a quick, fun and convenient way to view, select, enhance, print and share high quality photos on the go, without the need for a PC.

Grab it and go – share the fun of portable photo printing with your friends.

- · Never miss a moment take this stylish, compact and easy-to-use printer with you to parties, on holiday or anywhere else you'll want to share photos with friends.
- Enjoy the moment as it happens print photos in as fast as 60 seconds.
- Use the standard power supply or go fully mobile with the optional rechargeable battery or in-car adapter also recharges your internal battery.
- Other optional accessories include: carry case for printer, paper, cartridges and power lead.

Print without a PC direct from memory cards¹, cameras, flash drives and camera phones².

- Easy-to-use just insert memory card and print: slots for CompactFlash™, SmartMedia, Memory Stick, Secure Digital/MultiMediaCard and xD-Picture Card.
- Print directly from any PictBridge-enabled camera; also compatible with most USB flash drives.
- Print from camera phone, notebook, PDA, handheld or any other Bluetooth® wireless technology device².
- · Preview via 3.8 cm colour LCD and select photos using one-touch buttons. Print 9 frame sequences of still photos from video clips.

Turn snapshots into masterpieces - print long lasting, true-to-life colour or b/w photos4.

- Print bright, vivid photos that will last for generations³ with HP Vivera Inks.
- Save ink and money with HP inkjet cartridges designed for efficient ink usage.
- · Get better photos with HP Real Life technologies remove red-eye in-printer and bring detail out of the shadows with adaptive lighting.
- Print borderless 10 x 15 cm or panorama photos. Print professional b/w photos using optional HP 100 Grey Photo Inkjet Cartridge⁴.
- Edit and enhance photos on your PC using HP Image Zone.



¹ Memory card slots support CompactFlash™, SmartMedia, Memory Stick, Secure Digital/MultiMediaCard and xD-Picture Card. Also supports Memory Stick Duo (with adapter) and Mini SD (with adapter). Memory cards not included; please purchase separately.

² Wireless printing with optional HP bt300/450 Bluetooth wireless printer adapter (not included, please purchase separately).

³ Up to 82 years based on Wilhelm-Research.com light fade testing under glass using the HP 135 Tri-colour Inkjet Print Cartridge

on HP Premium Plus Photo Papers. For more information on additional permanence testing factors, visit http://hp.com/eur/faderesistance

⁴ Available with purchase of HP 100 Grey Photo Inkjet Print Cartridge; not included, please purchase separately.

Technical specifications

Print technology	HP Thermal Inkjet		
Print head nozzles	600 colour ink nozzles		
Print speed (As fast as # secs)	Document type Best Normal Draft 10 x 15 cm colour photo (photo paper) 90 60 45 Dependent upon type, print mode, and approximate figures. Exact speed will vary depending on the system configuration, software program, and photo density.		
Print quality	Colour: Up to 4800 x 1200-optimised dpi colour on HP Premium Photo Paper when printing from a computer and 1200-input dpi		
Colour technology	Photoret III		
Operating systems compatibility	Microsoft® Windows® 98, 2000 Professional, Me, XP Home and XP Professional; Mac OS X v 10.1.5, 10.2, 10.3		
Minimum system requirements	For all systems: 4x CD-ROM drive, SVGA monitor (800 x 600 with 16-bit colour), USB port and USB cable (not included) For PC systems: Pentium® II (or equivalent) or greater, Microsoft® Windows® 98, 2000 Professional, Me, XP Home and XP Professional, Microsoft Internet Explorer 5.5 or later, 600 MB free hard disk space (2 GB recommended), 64 MB RAM (256 MB recommended) For Mac systems: G3 processor or greater, Mac OS X v 10.1.5, 10.2, 10.3, 500 MB free hard disk space, 128 MB RAM (256 MB recommended)		
Memory	32 MB		
Printer languages	HP PCL 3 GUI, PML		
Recommended media weight	HP Photo Papers up to 280 g/m²		
Recommended media	Photo paper: 10 x 15 cm, plain paper accepted		
Media sizes	Standard: 10 x 15 cm, 10 x 30 cm		
Media handling/input	Sheets: Up to 20		
Media handling/output	Sheets: Up to 20		
Paper input trays	Standard: 1		
Power	Requirements: Input voltage 100 to 240 VAC (± 10%), 50/60 Hz (± 3 Hz) Supply type: External: power supply module Consumption: 12.2 watts average (printing), 6.7 watts average (non-printing)		
Interface and connectivity	1 USB port – compatible with USB 2.0 specifications, 4 memory card slots, PictBridge Optional: Bluetooth® printing with optional HP bt300/450 Bluetooth Wireless Printer Adapter		
Control panel	3.8 cm LCD display for image preview and selection. Enhanced control panel with "On", "Delete", "Print", "Cancel", "Select" butto		
Software included	HP Image Zone Software for Microsoft® Windows® and Macintosh, with HP Instant Share™ Software		
Dimensions (w x d x h)	Out of package: 220 x 116 x 116 mm; packaged: 300 x 194 x 235 mm		
Weight	Out of package: 1.17 kg; packaged: 2.1 kg		
Operating environment	Operating temperature: 0 to 45° C, recommended operating temperature: 15 to 35° C, operating humidity: 5 to 95% RH, recommended operating humidity: 20 to 80% RH, storage temperature: -30 to 65° C, storage humidity: 5 to 95% RH. Noise level per ISO 9296, sound power: LwAd 5.5 B(A), sound pressure: LpAm 55 dB(A)		
Safety	IEC 60950: third edition: 1999; EN 60950:2000; UL 1950/CSA22.2 No. 950, third edition: 1995; NOM 019-SFCI-1993; GB4943:2001		
Certifications	IEC 61000-4-2:1995, IEC 61000-4-3:1995, IEC 61000-4-4:1995, IEC 61000-4-5:1995, IEC 61000-4-6:1996, IEC 61000-4-11:1994, IATA 902, EN 55022 CISPR 22:1997, EN 55022 CISPR 22:1997, FCC Part 15 Class B		
Supplies life	C8766HE HP 135 Tri-colour Inkjet Print Cartridge (7 ml) 90 photos* C9363HE HP 134 Tri-colour Inkjet Print Cartridge (14 ml) 160 photos* *Based on 15% coverage for colour, in normal mode		
Warranty	One-year limited hardware warranty backed by HP service and support (Warranties may vary in European countries where legarequirements require a longer warranty period).		

Ordering information

Q6377C HP Photosmart 335 Compact Photo Printer, HP 135 Tri-colour Inkjet Print Cartridge (7 ml), power module with cord, 10 x 15 cm photo media sampler, index card kit, user's guide, setup poster, CD-ROM with HP Image Zone Software for Microsoft® Windows® and Macintosh including HP Instant Share™

	Optional accessories
Q3424A	HP Carrying Case for compact photo printers
Q3448A	HP Car Adapter
Q5599A	HP Battery for compact photo printers
Q3395A	HP bt300 Bluetooth Wireless Printer Adapter
Q6398A	HP bt450 Bluetooth Wireless Printer Adapter

	Inkjet printing supplies
Q7935HE	HP 135 Series Photo Pack 10x15 (100 Sheets)
C8766HE	HP 135 Tri-colour Inkjet Print Cartridge (7 ml)
C9363HE	HP 134 Tri-colour Inkjet Print Cartridge (14 ml)
C9368AE	HP 100 Grey Photo Inkjet Print Cartridge (15 ml)

Media	

Q1991A/Q1992A HP Premium Photo Paper, Glossy, 10 x 15 cm (20/60 sheets)

Q5479A/Q6601A HP Premium Photo Paper, Glossy, 10 x 15 cm borderless (20/60 sheets)

Q1979A/Q1980A HP Premium Plus Photo Paper, High-gloss, 10 x 15 cm (20/60 sheets)

Q2503A HP Premium Plus Photo Paper, High-gloss, 10 x 15 cm borderless (20 sheets)

Q2507A/Q2508A HP Premium Plus Photo Paper, Satin-matt, 10 x 15 cm (20/60 sheets)

Q6573A HP Premium Plus Photo Paper, high-gloss, 10 x 30 cm panorama (20 sheets)

Service and support

U4800A/E HP Care Pack service (3 years; return to depot service) – available in selected countries only

This printer and its replacement cartridges are designated for sale only in Commonwealth of Independent States (except Moldova), Mongolia, Middle East and Africa.

http://www.hp.com http://www.hp.com/go/photosmart

For more information, please call your local HP sales office or representative: Albania: +49 89 9396 1803; Algeria: +213 (0) 61 56 45 43; Austria: +43 (0) 810 00 60 80; Bahrain: 800 171; Belgium: +32 (02) 729 71 11; Bulgaria: +359 2 960 19 40; Bosnia-Herzegovina: +49 89 9396 1803; Commonwealth of Independent States (CIS): +(095) 923 50 01; Croatia: +385 1 606 02 00; Czech Republic: +420 261 10 81 11; Denmark: +45 45 99 10 00; Egypt: HP +202 345 13 52 or CPQ +202 792 50 70; Estonia: +372 6 813 820; Finland: HP Myyntipalvelu 010 217 2700; France: +33 (0) 826 800 400; Germany: +49 0180 532 62 22; Greece: +30 80 11 12 25 64 7; HP East Africa, Authorized Consultant: +254 20 271 6111; Hungary: +36 (1) 382 11 11; Iceland: +354 (1) 67 10 00; Ireland: +353 1 615 82 00; Israel: +972 9 830 48 48; Islay: Personal computer, Server Intele periferiche +39 02 92607 332), Esrver e workstooi UNIX, Storage, OpenView +39 02 92607 322; Kazaldhstan & Kyrgyzstan: +7 327 2 58 43 43; Liwit: +371 703 07 00; Lithuania: +370 5 2103 300; Macedonia: +49 89 9396 1803; Malta: +49 89 9396 1803; Middle East (Within UAE Toll Free): 800 45 20; Moldova: +49 89 9396 1803; Morocco (African Region): Call Centre +212 22 40 47 47, HP Sale Office +212 22 97 37; Netherlands: +31 (30) 222 2000; Nigeria: +334 1 26 26 720 / 1; Norway: +47 24 09 70 00; Poland: 0 801 522 622 and/or 00 48 565 77 00; Portugal: +351 (1) 301 73 437; Romania: +40 (21) 303 83 00; RSa: +8080 11 88 83; Russia: +7 095 797 37 97; Slovenia: +381 120 14 74; Saudi Arabbia: +800 897 14 33; Serbia and Monteaus: +81 120 14 20; Slovenia: +381 120 14 20; Slovenia: +380 14 490 61 20.













