

## Farnell Components

### CABLE

Item	Order No.	Type	Description	Colour
11a	60.7453-21 (Comprising 5m hank)	FLEXI-ZW 0,75	Highly flexible, twin-core, PVC insulated cable.	Black 632 7100
11b	60.7453-21 (Comprising 25m reel)	FLEXI-ZW 0,75	As above	Black 632 7111

- Nominal cross section: 2 x 0.75mm<sup>2</sup> / 18AWG
- Strand design: 196 x 0.07
- Conductor diameter: 1.25mm
- Insulation thickness: 0.45mm
- Outer diameter: 3.4mm (h) x 6.9mm (b)
- Current rating: 12 Amp
- Nominal voltage: 1000V
- Test voltage: 8000Vac
- Insulation: PVC
- Operating temperature: -10°C +70°C
- UL: UL approved for test leads, upto +60°C