

CE

IP54 SEALED

OPERATIONS PER KEY

**RESPONSIVE KEY ACTION** 

ESD PROTECTED

CE COMPLIANT

A

В

# Responsive keypads for industrial

## use.


Reliable data entry in sheltered outdoor or indoor locations.



### Ftorm<sup>®</sup> 3000 Series

### Responsive, reliable keypads for general service or sheltered outdoor use.

Utilising the proven Storm switch technology, these keypads are splashproof and suitable for use in most light, industrial applications.



### ELECTRICAL MATERIAL **Contact Bounce** 5ms (max) Casing General Service Polymer **Contact Resistance** 100 ohms (max) (mid grey) Insulation Resistance 50 Mohms (min) Keytops General Service Polymer 500V AC (max 60 secs.) Breakdown Voltage (light grey) Operating Voltage 24V DC (max) **Keytop Legends** Printed Gold on Nickel plated FR4 **Operating Current** 50mA (max) **Contact Circuit** MECHANICAL ENVIRONMENTAL FRE 2 million cycles (min) per key IP54 (when mounted **Operational Life** Water / Dust Sealed 1.4mm nominal to suitable enclosure) Kevtop Travel FM 39602 Actuation Force 180gms nominal Operational -10°C to +85°C Connector 0.1" pitch, gold plated square Temperature (Drv)

USA Office:

IP54 SEALED

OPERATIONS PE

Whilst every effort is made to ensure details are correct at time of production, specifications are subject to change without notice.

pin, male connector

Issue 2 – MAY 99 300-LIT-02

450-B Industrial Drive, Fort Collins, CO 80 Tel: 970-221 2201 Fax: 970-484 4078