

308316

**SPECIFICATION FOR 505/PWSM**

(1)	<b>PAPER</b>	<b>Width:</b> 58mm <b>Diameter:</b> 70mm Ø or less
(2)	<b>ADMISSIBLE PAPER</b>	<b>Diameter:</b> 80mm Ø or less
(3)	<b>MOTOR</b>	<b>Voltage:</b> 5V DC <b>Current:</b> 170mA or less (Average current in winding) 100mA or less (Average current non-winding)
(4)	<b>SHAFT TORQUE</b>	100g - cm (with friction clutch)
(5)	<b>DIRECTION OF WINDING</b>	As per attached drawing
(6)	<b>RELIABILITY</b>	More than 200 million lines
(7)	<b>TEMPERATURE HUMIDITY</b>	Room temperature Normal humidity
(8)	<b>EXTERNAL DIMENSION</b>	As per attached drawing
(9)	<b>NET WEIGHT</b>	320g

**SPECIAL COMMENTS FOR USE**

Please note the following point carefully:

- (1) Centre line of paper in printer mechanism, in paper roll and winder, must be in the same line.

Ref: OAW/6129/mlw

