

374 and 375 True-RMS AC/DC Clamp Meters

Work horse clamps with increased performance and flexibility

The new Fluke 374 and 375 clamp meters offer improved performance perfect for many current measurement situations. With True-RMS ac voltage and current measurements, the Fluke 374 and 375 can read up to 600 V and 600 A in both ac and dc modes. Additionally, both are compatible with the new iFlex™ flexible current probe (sold separately) which expands the measurement range to 2500 A ac and provides increased display flexibility, ability to measure around awkward sized conductors and improved wire access.



New

1000 V CAT III
600 V CAT II

**True
RMS**

Technical Data

Measurement capability

- 600 A ac and dc current measurement with fixed jaw
- 2500 A ac current measurement with iFlex™ flexible current probe (sold separately)
- 600 V ac and dc voltage measurement
- True-RMS ac voltage and current for accurate measurements on non-linear signals
- Frequency measurement to 500 Hz with both jaw and iFlex™ (Fluke 375 only)
- Resistance measurement to 60 kΩ (Fluke 375) or 6000 Ω (Fluke 374) with continuity detection
- Min, max, average and inrush recording to capture variations automatically
- 500 mV dc measurement range to interface with other accessories (Fluke 375 only)
- 1000 μF capacitance measurement

Features

- iFlex™ flexible current probe expands the measurement range to 2500 A ac while providing increased display flexibility, ability to measure awkward sized conductors and improved wire access
- CAT IV 600V, CAT III 1000 V safety rating
- Integrated low pass filter (Fluke 375 only) and state of the art signal processing allows for use in noisy electrical environments while providing stable readings



- Proprietary inrush measurement technology to filter out noise and capture motor starting current exactly as the circuit protection sees it
- Ergonomic design fits in your hand and can be used while wearing personal protective equipment
- Large, easy to read, backlight display automatically sets the correct measurement range so you do not need to change switch positions while taking a measurement
- Three-year warranty
- Soft carrying case

Specifications

Fluke 374 and 375	Range	Max Resolution	Accuracy
AC current via jaw	600 A	0.1 A	2 % ± 5 digits
AC current via iFlex™ (optional)	2500 A	0.1 A	3 % ± 5 digits
DC current	600 A	0.1 A	2 % ± 5 digits
AC voltage	600 V	0.1 V	1.5 % ± 5 digits
DC voltage	600 V	0.1 mV (375) 0.1 V (374)	1 % ± 5 digits
Resistance	60,000 Ω (375) 6000 Ω (374)	0.1 Ω	1 % ± 5 digits
Frequency (375 only)	500 Hz	0.1 Hz	0.5 % ± 5 digits
Capacitance	1 µF to 1000 µF	1 µF	1 % ± 4 digits
True-RMS		•	
Continuity		•	
Hold		•	
Backlight		•	
Min/Max		•	
Inrush		•	
Low pass filter		Fluke 375 only	
45 cm (18 inch) iFlex™ Flexible Current Probe		Optional accessory	
25 cm (10 inch) iFlex™ Flexible Current Probe		Optional accessory	
Wire capacity		34 mm	
Safety rating		CAT III 1000 V, CAT IV 600 V	

Models	Feature Changes
Old model: Fluke 337	
New model: Fluke 376	Includes all 337 features plus: • CAT IV 600 V, CAT III 1000 V • iFlex™ 2500 A ac • 1000 V ac/dc • mV dc • 60 kΩ • 1000 µF
Old model: Fluke 336	
New model: Fluke 375	Includes all 336 features plus: • CAT IV 600 V, CAT III 1000 V • Optional iFlex™ 2500 A ac • mV dc • 60 kΩ • 1000 µF • Min/Max/Avg
New model: Fluke 374	Includes all 336 features (except low pass filter) plus: • CAT IV 600 V, CAT III 1000 V • Optional iFlex™ 2500 A ac • Min/Max/Avg
Old model: Fluke 335	
New model: Fluke 374	Includes all 335 features plus: • CAT IV 600 V, CAT III 1000 V • Optional iFlex™ 2500 A ac • 600 A ac/dc • 1000 µF • Min/Max/Avg
New model: Fluke 373	Includes all 335 features (except inrush) plus: • CAT IV 300 V, CAT III 600 V • 1000 µF
Old model: Fluke 334	
New model: Fluke 374	Includes all 334 features plus: • CAT IV 600 V, CAT III 1000 V • Optional iFlex™ 2500 A ac • True-RMS • 600 A ac/dc • 1000 µF • Min/Max/Avg
New model: Fluke 373	Includes all 334 features (except inrush) plus: • CAT IV 300 V, CAT III 600 V • True-RMS • 1000 µF
Old model: Fluke 333	
New model: Fluke 373	Includes all 333 features plus: • CAT IV 300 V, CAT III 600 V • True-RMS • 600 A ac • 6000 Ω • 1000 µF

Ordering information

Fluke 374 True-RMS AC/DC
Clamp Meter

Fluke 375 True-RMS AC/DC
Clamp Meter

Optional accessories

i2500-10 iFlex™ Flexible Current
Probe 25 cm (10 inches)

i2500-18 iFlex™ Flexible Current
Probe 45 cm (18 inches)



Fluke. Keeping your world
up and running.®

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
Web: www.fluke.eu

For more information call:
In Europe/M-East/Africa +31 (0)40 2 675 200
or Fax +31 (0)40 2 675 222

Fluke (UK) Ltd.
52 Hurricane Way
Norwich, Norfolk
NR6 6JB
United Kingdom

Tel.: (020) 7942 0700
Fax: (020) 7942 0701
E-mail: industrial@uk.fluke.nl
Web: www.fluke.co.uk/clamps

©2010 Fluke Corporation.
Specifications subject to change without notice.
Pub_ID: 11665-eng

Modification of this document is not permitted
without written permission from Fluke Corporation.