

## Loudspeakers



Part Number	Diameter	External Depth	Impedance	Power Rating	Frequency Response		Output Power	Sound Level SPL
					Min	Max		
LS00433	6.5"	75 mm	8 ohm	45 W	40 Hz	7 kHz	60 W	87 dB
LS00434	8"	91 mm	8 ohm	70 W	30 Hz	3.5 kHz	100 W	89 dB
LS00435	10"	125 mm	8 ohm	85 W	30 Hz	4 kHz	150 W	87 dB
LS00436	12"	140 mm	8 ohm	100 W	26 Hz	3 kHz	200 W	91 dB