



MicroLink dLAN duo

Technical details

Standards	<ul style="list-style-type: none"> ▪ Ethernet specification IEEE 802.3, IEEE 802.3x, IEEE 802.3u ▪ Auto MDI / X ▪ Compatible to USB specification, rev. 1.1 ▪ Compatible to HomePlug standard 1.0
Protocols	CSMA/CD
Data transfer rate	14 Mbps
Transfer method	Asynchronous
Modulation	OFDM-84 carrier
Range	200 m via power circuit
Security	DES _{pro} encryption via power circuit
LEDs	<ul style="list-style-type: none"> ▪ 3 connectors (Link/Act 10 Ethernet, Link/Act 100 Ethernet, USB) ▪ 3 HomePlug status (Power, Act, Link)
dLAN connection	EURO power plug
Computer interface	Connector type: RJ 45 or USB (Universal Serial Bus) 1.1
Power consumption	3.3 W
Power supply	Integrated 110 – 230 V AC supply from plug socket
Temperature	Storage: -25 °C – 70 °C (= (-13)°F - 158°F) Operation: 0 °C -40 °C (= 32°F - 104°F)
Environment	10–90% humidity (non-condensing)
Operating systems	Includes, but not limited to, Windows [®] 98, Windows [®] Me, Windows [®] 2000, Windows [®] XP, Mac [™] OS X (Ethernet connector only), Linux [®] , and all TCP/IP operating systems
Approvals	CE compliant in accordance with all technical requirements for all EU countries and Switzerland: EN 55022; EN 55024; EN 60950

Sales information

Article number	01138 (DE/AT/CH/IT/FR), 01140 (B), 01142 (NL,ES)
EAN code	4250059611382 (DE/AT/CH/IT/FR), 4250059611405 (B), 4250059611429 (NL,ES)
Warranty	3 years
Service & Support Hotline	Tel.: 0180-5338656 (Germany only) E-mail: support@devolo.de In Austria, Belgium, France, Germany, Italy, the Netherlands, Spain, Switzerland and Great Britain—for further information such as telephone numbers see the enclosed support flyers
On-site Service	Tel.: 01805-665066 (Germany only)
Sales Info-line	Tel.: +49 (0)241-1827979 Fax: +49 (0)241-1827997 E-Mail: vertriebsinfo@devolo.de
Design	Wall plug plastic housing
Dimensions	80 x 63 x 37 mm (height x width x depth)
Weight	234 g
Packaging size	188 x 234 x 71 mm (height x width x depth)
Accessories	<ul style="list-style-type: none"> ▪ Ethernet cable RJ45-RJ45 (Cat 5) (3m) ▪ USB cable USB-A – USB-B (5m) ▪ Documentation: printed installation guide ▪ CD-ROM: USB driver (98, Me, 2000, XP, Linux) PDF manual, configuration software for Windows[®] 98, Windows[®] Me, Windows[®] 2000, Windows[®] XP, Linux[®], Mac[™] OS X For Windows: Monitoring tool MicroLink Informer, network sharing tool MicroLink Easyshare