



Part: 04450715  
 Series: 445 Series - PC Board Mount Fuseholder for ATO™ series Automotive Fuses  
 Technology: Fuse Holders, Blocks and Clips - Electronic and Automotive Types

<b>PARAMETERS</b>		
Package Type	Pkg Type	Fuseholder
Mount Method	Mount	PC Mount
Body Style for International Shock-Safe Fuseholders	Body	
Color of Device	Color	
For use with this UL Class or Fuse Type	Fuse Type	ATO
For use with this UL Class or Fuse Type	Fuse Type	258
Fuse Mounting Method	Fusemounting	Automotive Type Fuses
Indicating	Indicating	N
Maximum Current Rating	Max (A)	15.0000
AC Voltage Rating	Max VAC (V)	32
Max DC Voltage	Max VDC (V)	32
Mounting Type	Mounting	PC Mount
	special1	
	special2	
Terminal Style for International Shock-Safe Fuseholders	Terminal	
For use with UL Class ____ Fuses	UL Class	Supplementary Protection