

Micrometers Mechanical

LINEAR TOOLS micrometers are precision instrument for measuring small distances.

Special care in design and workmanship create a long lasting precision tool.

General specification for all mechanical micrometers unless otherwise stated:

- Accuracy conforms to DIN 863
- Hammertone blue baked enamel finish
- Tungsten carbide measuring faces
- Non-glare satin chrome barrel & sleeve
- Microfine graduations for accurate reading
- Micrometers above 25mm & 1" supplied with setting rod
- Spindle locking lever
- Spindle diameter 6.5mm
- Standard models have ratchet thimble
- Supplied in fitted case with adjustment tools
- Spindle diameter: 6.5mm
- Flatness of measuring faces: 0.00076mm
- Parallelism of measuring faces: 0.000125mm

Micrometer graduations:

- Metric: 0.01mm
- Imperial: 0.001"



All measuring tools (where applicable standard exists) can be supplied with UKAS certificate, prices upon request.

Outside Micrometers Metric DIN 863

TECHNICAL:

- Accuracy conforms to DIN 863
- Hammertone blue baked enamel finish
- Tungsten carbide measuring faces
- Non-glare satin chrome barrel & sleeve
- Microfine graduations for accurate reading
- Models above 25mm/1" supplied with setting rod
- Spindle locking lever
- Spindle diameter 6.5mm
- Standard models have ratchet thimble
- Supplied in fitted case with adjustment tools
- Flatness of measuring faces: 0.00076mm
- Parallelism of measuring faces: 0.000125mm

Micrometer graduations:

- Metric: 0.01mm
- Imperial: 0.001"



LDS1024



Order Code	Description/ Size	List Price		Order Code	Description/ Size	List Price	
50-100-025	0-25mm	£19.95	P	50-100-001	0-1"	£19.95	P
50-100-050	25-50mm	£27.30	P	50-100-002	1-2"	£27.30	P
50-100-075	50-75mm	£30.90	P	50-100-003	2-3"	£30.90	P
50-100-100	75-100mm	£33.00	P	50-100-004	3-4"	£33.00	P
50-100-125	100-125mm	£37.60	P	50-100-005	4-5"	£37.60	P
50-100-150	125-150mm	£43.00	P	50-100-006	5-6"	£43.00	P
50-100-175	150-175mm	£50.20	P	50-100-007	6-7"	£50.20	P
50-100-200	175-200mm	£57.00	P	50-100-008	7-8"	£57.00	P
50-100-225	200-225mm	£62.20	P	50-100-009	8-9"	£62.20	P
50-100-250	225-250mm	£67.50	P	50-100-010	9-10"	£67.50	P
50-100-275	250-275mm	£72.80	P	50-100-011	10-11"	£72.80	P
50-100-300	275-300mm	£78.00	P	50-100-012	11-12"	£78.00	P

