

Lanterns

UK48 Professional Swivel Headed Lantern

in Safety Yellow (also available in orange - see right hand insert)

- Reflector diameter 86mm (3 3/8")
- High performance, bi-convex **BeamMaster** lens
- Head swivels 135° for flexible beam direction
- High impact, Co-polymer body
- Weatherproof
- Micro-switch operation
- Convenient shoulder strap
- Operates using a 996/4R25 6v lantern battery, UK251 rechargeable battery, or UK300 plug-in rechargeable battery (not included - see page 7)
- Bulb: 4.8v Krypton



UK58

UK48



UK240



UK240 Professional Lightweight Rechargeable Lantern System

- Exceptional performance from this extremely lightweight lantern which weighs less than 525g due to UNI-LITE's latest technology
- Reflector diameter 86mm (3 3/8")
- High performance bi-convex **BeamMaster** lens
- High impact Co-polymer body with charging point at rear
- Micro-switch operation
- Comes complete with rapid charge rechargeable lantern battery which can be fully charged in 6 hours
- Simple to use charger which plugs directly into a conventional domestic socket
- Bulb: 4.8v Krypton

UK200



UK200 Professional Heavy Duty Floating Lantern in Grey

The Professional Heavy Duty Floating Lantern is available in two colours

- Reflector diameter 108mm (4 1/4")
- High performance, bi-convex **BeamMaster** lens
- High impact Co-polymer body
- Weatherproof - floats beam upright in water
- Micro-switch operation
- Convenient removable wrist strap
- Operates using a 996/4R25 6v lantern battery, UK251 rechargeable battery, or UK300 plug-in rechargeable battery (not included - see page 7)
- Bulb: 4.8v Krypton

UK49 Professional Heavy Duty Floating Lantern in Safety Yellow



UK49