

LCR55A Inductance, capacitor and resistor tester

- Measures inductance, capacitance, resistance, transistors, diodes and microwave diodes

- Wide measurement ranges
- Data hold, max hold and auto-off
- Ships with protective holster, test leads and threaded alligator clips



AVAILABLE SEP-07

FEATURES	CR50A	LCR55A
Resistance	0.01 Ω - 20 M Ω , ± 1.0 %	0.01 Ω - 20 M Ω , ± 0.5 %
Capacitance	0.1 pF - 20,000 μ F, ± 0.5 %	0.1 pF-2000 μ F, ± 1.0 %
Inductance	N/A	0.1 μ H-200 H, ± 5.0 %
Transistors	N/A	Hfe, I _{ceo} (NPN, PNP)
Diodes	Yes	Std (3 V) & microwave oven (8 V)
Continuity test	Yes	Yes