

Type	Cell	Size	Glass size	Weight	Max-Power	Max-Power Voltage	Max-Power Current	Open-Circuit Voltage	Short-circuit Current
Module	Mono/Poly	mm	mm	Kg	W	V	A	V	A
SR220-96	125 Mono/Poly	1067*1601*46	1061*1593	19.5	220	46	4.79	57	5.19
SR210-96	125 Mono/Poly				210	46	4.57	57	4.98
SR200-96	125 Mono/Poly				200	46	4.35	57	4.72
SR180-72	125 Mono/Poly	808*1581*46	802*1574	15	180	34	5.3	43	5.7
SR175-72	125 Mono/Poly				175	34	5.15	43	5.5
SR170-72	125 Mono/Poly				170	34	5	43	5.4
SR165-72	125 Mono/Poly				165	34	4.86	43	5.3
SR160-72	125 Mono/Poly				160	34	4.71	43	2.1
SR185-48	156 Mono/Poly	997*1337*46	991*1329	15.2	185	23	8.05	29	8.6
SR175-48	156 Mono/Poly				175	23	7.61	29	8.1
SR165-48	156 Mono/Poly				165	23	7.18	29	7.6
SR130-36	156 Mono/Poly	678*1484*40	1478*673	11.5	130	17	7.65	21.6	8.13
SR120-36	156 Mono/Poly				120	17	7.06	21.6	7.72
SR100-48	156 Mono/Poly	672*1196*40	667*1190	9.24	100	17	5.89	21.6	6.26
SR85-36	125 Mono/Poly	554*1205*40	549*1199	7.5	85	17	5	21.6	5.31
SR80-36	125 Mono/Poly				80	17	4.71	21.6	5.08
SR75-36	125 Mono/Poly				75	17	4.42	21.6	4.83
SR70-36	125 Mono/Poly				70	17	4.12	21.6	4.63
SR60-36	125 Mono/Poly	544*908*40	539*902	5.5	60	17	3.53	21.6	3.81
	156 Mono/Poly	696*783*40	776*690	6					
SR50-36	125 Mono/Poly	544*786*28	539*780	4.5	50	17	2.95	21.6	3.13
	156 Mono/Poly	668*651*28	663*645	4.6					
SR40-36	125 Mono/Poly	544*638*28	539*632	3.6	40	17	2.36	21.6	2.54
	156 Mono/Poly	534*668*28	528*663	3.7					
SR30-36	125 Mono/Poly	544*507*28	501*539	2.9	30	17	1.77	21.6	1.91
	156 Mono/Poly	426*668*28	420*663	3					
SR20-36	125 Mono/Poly	294*637*28	289*631	2	20	17	1.18	21.6	1.27
	156 Mono/Poly	366*539*28	361*533	2.1					
SR10-36	G-Mono/Poly	356*352*28	346*351	1.5	10	17	0.59	21.6	0.64
SR5-36	G-Mono/Poly	194*385*28	189*379	0.8	5	17	0.3	21.6	0.33