

• Horn / light combination

• Can be triggered separately



## TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Height):	70 mm x 256 mm
Housing:	ABS, high impact, grey
Dome:	Polycarbonate, transparent
Socket:	B 15 d, max. 7 Watt
Connection:	Screwable connection max. 2.5 mm <sup>2</sup> cable entry up to ø 9 mm
Duty cycle:	100 %
Bulb included in assembly	

## ORDER SPECIFICATIONS:

Voltage	12 V =	24 V =	24 V -	230 V -
Current consumption	610 mA	320 mA	320 mA	50 mA
red	580 152 54	580 152 55	580 152 65	580 152 68
yellow	580 352 54	580 352 55	580 352 65	580 352 68

## TECHNICAL DIAGRAMS

see page 117



580

Horn/Light Combination

