

Easy Break **Terminal Strips****Features**

- Easy snapped to required number of poles
- No remaining burrs
- No tools needed to cut to length
- Moulded from PA6 to UL94V-2
- Supplied natural colour. Black optional
- Supplied with screws in raised position

Specification

Voltage	450V
Temperature	-30 to 110°C
Moulding	PA6 UL94V-2
Inserts	Nickel plated brass
Screws	Zinc plated steel
No. of poles	12

Type No.	Length A (mm)	Width B (mm)	Height C (mm)	D	E	Screw
CTSOS431	95.5	17.5	12.75	8	3	M3
CTSOS433	118.1	19	13.85	10	3.5	M3
CTSOS434	142.2	20.8	16.6	12	4.4	M3.5
CTSOS435	159.9	23	20.6	13.5	6	M4
CTSOS438	179.3	26	27.85	15	8.2	M5

Insert Diameter	Ø3mm	Ø3.5mm	Ø4.4mm	Ø6mm	Ø8.2mm
Rated Connecting capacity	2.5mm ²	6mm ²	10mm ²	16mm ²	35mm ²
Conductors minimum section	1mm ²	2.5mm ²	4mm ²	6mm ²	16mm ²
Test current	24A	41A	57A	76A	125A

