



DATE	REV	DESCRIPTION	BY	CHKD



Marking: (LP009) FTP CAT.5E PATCH ISO/IEC 11801 & EN 50288
 3P VERIFIED FOR GIGABIT ETHERNET 26AWG×4P TYPE
 CM(UL)C(UL) CME E164469-F3




orange 1	green 2
white/orange	white/green
blue 3	brown 4
white/blue	white/brown

Conductor	Bare Copper 26AWG 7/0.15a ± 0.15mm
Insulation	Thickness MIN at any point 8.15mm MAX AVG 0.25mm Diameter 0.70a ± 0.05mm
Jacketing	Thickness MIN at any point 80mm MAX AVG 0.80mm Diameter 8.5 ± 0.2mm

WIRE	Draka Cat.5E FTP
Plug	RJ45 AMP x2
Length	XX
COLOR	Gray825

Lead	<1000ppm
Cadmium	<100ppm
Mercury	<1000ppm
Chromium	<1000ppm
PBB	<1000ppm
PBDE	<1000ppm

PA/R	PINOUT		
	P1 (T568B)	WIRE	P2 (T568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	4
	5	WHT/BLU	5
4	7	WHT/BRN	7
	8	BRN	8



ROHS compliant from Nov. 2005

Unless specified on the drawing, tolerances are per the follows:
 . ± 1
 .X ± 0.2
 .XX ± 0.05

Videk Part No: 3962-xx

3RD		DRAW. NO	ITEM	DEPARTMENT	DRAW	DATE	2006/03/20
		SCALE	CHECKER			APPROVAL	
		UNIT	MM	SHEET	1	OF	1