

DURACELL®

CEF80

1 - Hour Charger

NiMH



150 mm (L) X 84 mm (W) X 42 mm (H)

Class 2 Battery Charger	
Battery Type:	HR03 AAA or HR6 AA
Average Weight:	143 gm (5 oz.)
Input:	100-240V (AC) 50/60 Hz
Output:	NiMH (4AA) 1.4V DC 2A NiMH (4AAA) 1.4V DC 1.0A
Operating Temperature Range:	0°C to 50°C (32°F to 122°F)

Charge Termination is based on -dV, temperature and/or built-in timer.

Indicators: Charge LEDs

(4 independent channels for AA, switchable for AAA cells)

Red - Charging.

Completed Charging - LED's OFF

Flashing Red indicates error - Abnormal battery or abnormal temperature.

DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

Charge rate and time is dependent on the battery discharge state and operating temperature .
Please refer to the battery instructions for charging details.