

6.00069.50 PowerMaxx Li Pro

7.2 Volt Cordless Drill / Screwdriver PowerMaxx Li Pro

- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Motor with integrated air cooling
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Spindle stop gear for manual turning of screws
- Spindle with hexagon recess for screwdriver bits
- Pistol grip for optimum power transmission in direction of drilling
- Fatigue-free operation due to perfect ergonomics
- Rubber-coated handle provides a comfortable non-slip grip for the user
- High service life due to 3-level planetary metal gears
- Sturdy die cast gearbox housing for long service life
- Powerful Li-Ion battery pack. No memory effect!
- Charger (charge time approx. 1 hours)

Comparative device characteristics

Type of battery pack	Li-Ion
Battery pack voltage	7,2 V
Capacity of battery pack	2,2 Ah
Maximum torque, hard	16 Nm
Drilling capacity in	
- Steel	3 mm/3 m/3 mm
- Wood	6,5 mm/6,5 mm/6,5 mm
No-load speeds	0 - 250/0 - 750 /min
Drilling spindle thread	1/2" - 20 UNF
Chuck capacity	0,5 - 6,5 mm
Weight (including battery pack)	0,73 kg

Scope of delivery

quick-action keyless chuck Futuro Plus, screw-type angle attachment, 2 Li-Ion battery packs (7.2 V/2.2 Ah), charger LC 60, Carry case