

GP BATTERIES UK Ltd.

Specification Sheet

Rechargeable NiMH Battery

Type. GP210AFH (AF Cell)

Farnell Part No. 604-550

Discharge:

Nominal Voltage ----- 1.2

End of Discharge voltage ----- 1.0

Nominal Capacity ---- 2100 mAh (0.2CA Rate) at 20° C

Typical Capacity ----- 2300mAh (0.2CA Rate) at 20° C

Capacity at 2CA ---- 2000 mAh at 20° C


Capacity at 3CA ---- 1950 mAh at 20° C

Internal Resistance -- 16 mOhm

Weight ----- 36 grams

Life ----- 500-1000 cycles at 20° C IEC

dims.
mm max




Charge:

Charge Current ----- 210 mA

Charge Time ----- 14 - 16 hrs

Trickle Charge ----- 105 mA cont.



Temperature Range:

Charge ----- 0 to 45° C

Discharge ----- -20° C to +50° C

Storage ----- -20° C to +35° C