


DRAWING NO
TDS-57
SH. A



TOOL No	ITEM NO	RANGE MM	OVERALL LENGTH	HEAD DIAMETER	SHANK DIAMETER	SHANK LENGTH	APPROX WEIGHT
DC 25	7015057	2-5	45mm	10mm	6mm	32mm	9g
DC 510	7015069	5-10	48mm	14mm	8mm	30.5mm	18g
DC 1015	7015070	10-15	65mm	21mm	10mm	37.5mm	48g
DC 1520	7015082	15-20	84mm	27.5mm	12mm	48mm	92g
DC 2025	7015094	20-25	102mm	35mm	15mm	56.5mm	190g
DC 2530	7015033	25-30	115mm	44mm	15mm	55mm	310g
DC 3035	7015045	30-35	127mm	48mm	15mm	60.5mm	370g

SET REF	ITEM NO	CONTAINS TOOLS			OVERALL DIMENSIONS OF METAL CASSETTE	APPROX WEIGHT
DC S1	7015628	DC 25	DC 510	DC 1015	DC 1520	580g
					158mm x 111mm x 35mm	

NOTE: WEIGHTS OF SETS
INCLUDE PLASTIC DIP
FOR ALL TOOLS

MOD NO	MOD NOTE REF NO	DATE OF MOD
A	MOD 1504	05-01-93
MATERIAL		
BM2 HSS		
FINISH		
BLUE ALL OVER EXCEPT FOR GROUND SHANK & CUTTING PORTION		
UNCONTROLLED DOCUMENT		
REMARKS		
THIS DRAWING IS FOR CUSTOMER COMMUNICATION & CATALOGUE DATA ONLY		
DATE	CATALOGUE REF.	
9-1-91	SEE	
DRAWN K. JACKSON	TOOL NO	
CHECKED A. KELSEY	&	
DO NOT SCALE		SET REF
TITLE HSS HOLE TYPE DEBURRING CUTTERS		
COMPUTER FILENAME : TDS57		DRAWING NO
		TDS-57
G & J HALL Ltd.		SH. MOD. A

1015057 → PDS