

PACITEC®

8"



These new PacTec styles are ideal for a variety of handheld applications, including test equipment, meters, data entry terminals, and more. The various sizes have been designed to work with a

wide variety of LCDs, LEDs, and graphic displays. A waterproof "O" ring is available for NEMA 4X applications (not available on TR Models).

STANDARD OPTIONS

- Insert tooling areas
- Battery compartment
- Flame retardant materials
- EMI/RFI shielding
- Connector cutouts
- LCD adapters/bezels
- Custom panels & overlays
- Soft rubber protective holster
- 4AA, (2)9VB, 6AA availability
- Standard and custom membrane switches



T SERIES	WIDTH	LENGTH	HEIGHT
TR-9VB/2AA	4.40/3.30	7.70	1.25
TS	3.29	7.27	1.25
TS-9VB/2AA	3.29	7.27	1.25
TT	4.44/3.29	8.52	1.15/1.50
TT-9VB/2AA	4.44/3.29	8.52	1.15/1.50
TT1-(2)9VB/4AA	5.45/3.30	8.40	2.42/2.88
TT2-5AA	4.60	10.29	2.25/2.38

All dimensions are outside dimensions-in inches T-Series units are available with a gasket for water-proofing the unit. Add G to the end of the part number when requesting a gasket.