

This Drawing is the property of J.S.T.(U.K.) Ltd.  
It must not be copied or used for manufacturing  
without written permission from J.S.T.(U.K.) Ltd.

**UNCONTROLLED  
CUSTOMER ISSUE**

# Page 1 / 2


CS-63N004V0	63N004V0	PA66	UL94V-0	Natural	110	--	
CS-63N004STY	63N004STY	PA46	UL94V-2	Natural	150	--	
01022-250 Red	63N304	PA66	UL94V-2	Red	110	E172855 (M)	
01022-250 Green	63N404	PA66	UL94V-2	Green	110	E172855 (M)	
01022-250 Brown	63NMR04	PA66	UL94V-2	Brown	110	E172855 (M)	
01022-250 Blue	63N604	PA66	UL94V-2	Blue	110	E172855 (M)	
01022-250 Black	63N504	PA66	UL94V-2	Black	110	E172855 (M)	
01022-250	63N004	PA66	UL94V-2	Natural	110	E172855 (M)	
JST Part Number	Mfg Number	Material	Flame Class	Colour	Max Operating Temp (°C)	UL Card No.	//

Revision Record		
	Add suffixes; 304,004STY, 004V0	31.10.02
	Add suffixes; 004,504,604,MR04,404	31.10.02
Modification Detail		Date
<b>JST</b>		


Part Description & General Details:		
Housing for 6.3 (.250) receptacle. Applicable JST terminal; STO-**(*)-250*(-*)		
<b>Series:</b>	63 Series	
<b>Drawing Ref:</b>	CS63N004-241194	
<b>Issues by:</b>	ZG	31.10.02
<b>Approved by:</b>	AR	31.10.02

This Drawing is the property of J.S.T.(U.K.) Ltd.  
It must not be copied or used for manufacturing  
without written permission from J.S.T.(U.K.) Ltd.

**UNCONTROLLED  
CUSTOMER ISSUE**



*Sez. A-A*



Revision Record		
Add suffixes; 304,004STY, 004V0	31.10.02	
Add suffixes; 004,504,604,MR04,404	31.10.02	
Modification Detail	Date	
<b>JST</b>		

Part Description & General Details:		
Housing for 6.3 (.250) receptacle. Applicable JST terminal; STO-**(*)-250*(-*)		
<b>Series:</b>	63 Series	
<b>Drawing Ref:</b>	CS63N004-241194	
<b>Issues by:</b>	ZG	31.10.02
<b>Approved by:</b>	AR	31.10.02