

305-3544

Parallel Entry Cable Ties PE Range


- Low profile design
- Easy insertion
- 2 sizes (with R prefix) have releasable catch
- Standard colour - weather resistant black



Product Reference	Length mm	Width mm	Min Tensile Strength lbs	Max. Cable Bundle Dia. mm
PE180	180	9	75	42
RPE275	275	9	100	69
RPE350	350	9	100	92
PE530	530	9	100	146

LPH Range

- Flexible nylon 6.6
- High integral tensile strength
- Weather resistant black as standard



Product Reference	Length mm	Width mm	Min Tensile Strength lbs	Max. Cable Bundle Dia. mm
LPH175	175	9	70	40
LPH275	265	9	108	62
LPH350	335	9	108	92

HellermannTyton
Cable Management Products