


Type	Size	Description	Part No.
Incandescent	T3.8 (T-1 <sup>1</sup> / <sub>5</sub> )	Axial Wire Terminal Lamp	(see table)



Drawing not to scale  
All dimensions in mm

### PHOTOMETRY DATA

Farnell Part No.	SLI P/N	Lamp Rating	Test Volts	Current (mA)			Light Output (Lm)			Fil Shape	Life (Hrs)
				Min	Nom	Max	Min	Nom	Max		
620701	3820AL	5-8V 0.6W	6	90	100	110	1.4	1.9	2.4	C-8	5000
620713	3890AL	10-15V 0.6W	12	50	55	60	1.7	2.3	2.9	C-8	5000

### NOTES:

- 1) Lead wires 0.30mm diameter with tinned finish.