



GP BATTERIES UK Ltd.

Specification Sheet

Rechargeable NiCd Battery

Type. GP22AAAK (AAA Cell)

Farnell Part No. 521 530

Discharge:

Nominal Voltage ----- 1.2

End of Discharge voltage ----- 1.0

Nominal Capacity ---- 220 mAh (0.2CA Rate) at 20° C

Typical Capacity ----- 250mAh (0.2CA Rate) at 20° C

Capacity at 2CA ---- 190 mAh at 20° C

Capacity at 3CA ---- 143 mAh at 20° C

Internal Resistance -- 80 mOhm

Weight ----- 10 grams

Life ----- 500-1000 cycles at 20° C

Charge:

Charge Current ----- 22 mA

Charge Time ----- 14 - 16 hrs

Trickle Charge ----- 11 mA cont.

Temperature Range:

Charge ----- 0 to 40° C

Discharge ----- minus 20° C to 50° C

Storage ----- minus 20° C to 35°

dims.
mm max

