

908-241/253/289/290

Key – Waterproof to IP67

A pen-type thermometer- with a range of optional screw-in K-type thermocouple probes suitable for general purpose/immersion, penetration, gas/air and surface temperature measurements. Temperature range is from -40 to +550°C with 1°C resolution and a fast response time. Probes are rugged ASI 316 stainless steel to resist chemicals and high temperatures.

A soft case is available as an optional extra which will hold the thermometer and four probes.

Technical Specification

Range	-40 to +550°C		
Resolution	1°C		
Accuracy	±2°C		
Battery life	700 hours		
Batteries	3 x 1.4V		
Dimensions	142 x 29 x 15		
Weight	80g		
Probes	Length	Diameter	Time Constant
General purpose	170mm	3mm	20 secs
Penetration	130mm	3mm	20 secs
Gas/Air	175mm	3mm	20 secs
Surface	210mm	3mm	20 secs

Pen Type

