



Z2823, FEC 177-197, 12VA clamp mounted transformer.
Input 0-110V, 0-110-130V, for series/parallel connections for 110, 220, 240V input.
Output 18V @ 0.33A twice for series/parallel connection to give 36V @ .33A or 18V @ .66A.
Off load (outputs in series) at nominal inputs = 41.1V Magnetising (no load input) current < 50mA

Z2295, FEC 141-479, 6VA clamp mounted.
Input as above.
Output 15V @ 0.2A twice for series/parallel connection to give 30V @ 0.2A or 15V @ .4A.
Off load output (series connected) at nominal input = 41.6V
Magnetising current < 31mA.