

312-1770

SPECIFICATION AND APPROVALS

- RFA#11679 (FARNELL CODE : N/A)
- 1) Model Number : Series 43A B/B-S with 'Blue In-Lady' on Button, QC. UL/CSA/VDE
- 2) Description : Rocker Switch
- 3) Name of Manufacturer: Swann Industries Pte Ltd
- 4) Approvals :
- | Approval | Cert. No. | Rating |
|----------|-----------|---|
| UL | E59618 | 15A 125VAC
7.5A 250VAC
3A 120V
6A 125/ 250VAC*
6A 28 VDC*
6A 14VT* |
| CSA | LR52381 | 15A 125VAC
8A 250VAC
0.5HP 125VAC |
| VDE | 93563 | 6A 125/ 250VAC*
10(4)A 250VAC |
- * with unplated terminals
- 5) Contact Resistance : $20 \times 10^{-3} \Omega$
- 6) Insulation Resistance : $> 50 \times 10^6 \Omega$
- 7) Dielectric Strength : Up To 3.5kVAC
- 8) Mechanical Endurance: $> 100,000$ cycles
- 9) Circuit : SPST, SPDT.
Illumination (Optional).
- 10) Recommended Panel Cut-Out :
- | Thickness (mm) | Cut-Out Size (mm) |
|----------------|-------------------|
| 1.0 (min) | 28.6 x 14.0 |
| 3.0 (max) | 28.8 x 14.0 |
- 11) Terminal : 6.35mm Quick Connect
Leaded Terminal
Solder Tail
PC Tail

Issued by :






Date :

18 JUN 97

© COPYRIGHT THIS DRAWING IS ISSUED BY SWANN INDUSTRIES PTE LTD ON THE UNDERSTANDING THAT IT IS STRICTLY CONFIDENTIAL AND MAY NOT BE REPRODUCED OR UTILIZED IN ANY WAY WITHOUT PRIOR WRITTEN PERMISSION.


312-1770



APPROVALS



SERIES 43A B/B-S 'Blue In-Lay' on Button, QC, UL/CSA/VDE

Tolerances Unless Noted		Scale	2 : 1	(FARNELL NO. N/A)		
Whole No.	± 0.23	Material	—	Part No.	RFAN11679	
1 Place Decimal	± 0.13	Finishing	—	Title SERIES 43A SCALLOP BUTTON		
2 Place Decimal	± 0.08	 SWANN INDUSTRIES PTE LTD		Drawn	CHRIS	
Angles	± 1°			Checked		28.9.98
DO NOT SCALE				Approved		