



SAFETY DATA SHEET
ROEBUCK LEMON FLOOR GEL CLEANER 5L

Page 1
Issued: 17/10/2002
Revision No: 1

1. IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING

Product name: ROEBUCK LEMON FLOOR GEL CLEANER 5L

Product code: DF009

Use / description of product: No significant hazard.

Company name: Dysys Hygiene Systems
2 Rainow Mill Cottage
Ingersley Vale, Bollington
Macclesfield
SK10 5BP
Tel: 01625 560508
Fax: 01625 571011

2. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous ingredients: 1161130 10-30%
[-] R10; [Xi] R36/38

3. HAZARDS IDENTIFICATION

Main hazards: No significant hazard.

4. FIRST AID MEASURES (SYMPTOMS)

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4. FIRST AID MEASURES (ACTION)

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

5. FIRE-FIGHTING MEASURES

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

Exposure hazards: In combustion emits toxic fumes.

Protection of fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

[cont...]

SAFETY DATA SHEET
ROEBUCK LEMON FLOOR GEL CLEANER 5L

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

7. HANDLING AND STORAGE

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

State: Liquid

Colour: Yellow

Odour: Characteristic odour

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Soluble

Viscosity: Highly viscous

pH: 8-10

10. STABILITY AND REACTIVITY

Stability: Stable under normal conditions.

Conditions to avoid: Heat.

Materials to avoid: Strong oxidising agents. Strong acids.

Haz. decomp. products: In combustion emits toxic fumes.

11. TOXICOLOGICAL INFORMATION

Routes of exposure: Refer to section 4 of SDS for routes of exposure and corresponding symptoms.

12. ECOLOGICAL INFORMATION

Mobility: Readily absorbed into soil.

Persistence and degradability: Biodegradable.

Bioaccumulative potential: No bioaccumulation potential.

Other adverse effects: Negligible ecotoxicity.

13. DISPOSAL CONSIDERATIONS

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

14. TRANSPORT INFORMATION**ADR / RID****UN no:** -**Shipping name:** "NOT SUBJECT TO ADR"**IMDG / IMO****UN no:** -**IATA / ICAO****UN no:** -**15. REGULATORY INFORMATION****Hazard symbols:** No significant hazard.**Note:** The regulatory information given above only indicates the principal regulations specifically applicable to the product described in the safety data sheet. The user's attention is drawn to the possible existence of additional provisions which complete these regulations. Refer to all applicable national, international and local regulations or provisions.**16. OTHER INFORMATION****Risk phrases used in s.2:** R10: Flammable.
R36/38: Irritating to eyes and skin.**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.