

(6223)

(ne52739)



Volex Inc.

3-CONDUCTOR POWER SUPPLY CORDS



- NEMA 5-15P Molded PVC Grounding Plug PH-290B, PH-185, or PH-173
- Rated 60°C; 125V, North American Color Coding, UL Listed, CSA Certified

TYPE SVT AND SJT PVC JACKETED

Stock No.	Type	AWG (Stranding)	Nom. O.D.	L	Rating	Plug	Cord
36F1821	17237	18 (42 × 34)	0.246"	6'	1250/10	290B	SVT
36F1822	17239	18 (42 × 34)	0.246"	8'	1250/10	290B	SVT
36F957	17405	18 (16 × 30)	0.315"	6'	1250/10	290B	SJT
36F958	17407	18 (16 × 30)	0.315"	8'	1250/10	290B	SJT
36F1251	17276	16 (26 × 30)	0.340"	20'	1625/13	185	SJT

TYPE SV AND SJ RUBBER AND SJO NEOPRENE JACKETED

Stock No.	Type	AWG (Stranding)	Nom. O.D.	L	Rating	Plug	Cord
36F1038	17238	18 (42 × 34)	0.246"	8'	1250/10	290B	SV
36F842	17406	18 (16 × 30)	0.315"	6'	1250/10	185	SJ
36F857	17408	18 (16 × 30)	0.315"	8'	1250/10	185	SJ
36F959	17409	18 (16 × 30)	0.315"	8'	1250/10	185	SJO
36F960	17412	18 (16 × 30)	0.315"	12'	1250/10	185	SJ
36F843	17419	16 (26 × 30)	0.340"	9'	1625/13	185	SJ
36F961	17422	16 (26 × 30)	0.340"	12'	1625/13	185	SJ
36F849	17425	16 (26 × 30)	0.340"	15'	1625/13	185	SJ
36F1823	17629	14 (41 × 30)	0.380"	9'	1875/15	173	SJ
36F1253	17635	14 (41 × 30)	0.380"	15'	1875/15	173	SJ